

Product data sheet

GC 307+ *



Non-contact proximity switch for activating automatic doors

AREAS OF APPLICATION

- Non-contact activation of automatic swing, sliding, folding, revolving and curved sliding doors
- Interior and external doors
- Rooms with high hygiene demands

PRODUCT FEATURES

- Doors can be opened without a requirement for tactile perception
- External input for LED colour change
- Detects persons and objects in a detection area of 10 - 60 cm
- Scanning ranges adjustable to make environmentally and user-specific adjustments
- Hand-height mounting ensures convenient, barrier-free access
- Can also be installed behind tiles or glass
- Adjustable via DIP switch and remote control; acoustic feedback, LED colours, LED animations, pulse/toggle mode
- WC control function for locking and automatic unlocking of toilets

TECHNICAL DATA

Productname	GC 307+ *
Technology	Electromagnetic radar waves
Operating voltage	12-24 V DC +30% / -10% / 12-24 V AC ± 10%
Output	Electrical relay
IP rating	IP65
Cable connection type	Screw terminal
Adjustability	Per DIP switch, with remote control
Installation height	at hand level
Transmission frequency	24.15 GHz
Service temperature	-20 - 55 °C
Standard conformity	RED 2014/53/EU, RoHS 2011/65/EU

VARIANTS / ORDER INFO

Designation	Description	Ident-No.	Colour	Dimensions	Type of installation
GC 307+ (hand icon) *	Proximity switch for the activation of / automatic doors	195727	alpine white	80 x 80 x 21 mm	
GC 307+ (WC icon) *	Proximity switch for the activation of / automatic doors / Suitable for Powerturn, EMD, and standard sliding doors	195751	alpine white	80 x 80 x 21 mm	
GC 307+ (hand icon) *	Proximity switch for the activation of / automatic doors	193226	alpine white	80 x 80 x 8 mm	Flush-mounted installation
GC 307+ (WC icon) *	Proximity switch for the activation of / automatic doors / Suitable for Powerturn, EMD, and standard sliding doors	195750	alpine white	80 x 80 x 8 mm	Flush-mounted installation

GC 307+ *



* The products designated above may vary in form, type, characteristics, function, or availability depending on the country. Please get in touch with your GEZE contact person if you have any questions.